

Part Number : [1300130074](#)

Product Description : Mini-Change A-Size Receptacle, 2 Poles, 1/2" - 14 NPT Threads, Female (90°) to 16 AWG Leads, 0.305m (1.0') Length



Series Number : 130013

Status : Active

Product Category : Circular Industrial Connectors

Engineering Number : 1R2005A20A120

Documents & Resources

Drawings

[1300130074_sd.pdf](#)

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Circular Industrial Connectors
Series	130013
Description	Mini-Change A-Size Receptacle, 2 Poles, 1/2" - 14 NPT Threads, Female (90°) to 16 AWG Leads, 0.305m (1.0') Length
IP Rating	IP67
NEMA Rating	NEMA 6
Product Name	Mini-Change
Type	Single Ended (pigtail)
UPC	78678842320

Agency

CSA	LR6837
UL	E152210

Electrical

Current - Maximum per Contact	13.0A
Voltage - Maximum	600V AC/DC

Physical

Coupling Type	External Thread
Gender	Female
Keyway	Single
Length	0.305m
Material - Component	Zinc Die-Cast with Black Epoxy
Mounting Thread Size	1/2" - 14 NPT
Orientation	90° Angle
Panel Mount	N/A
Poles	2
Temperature Range - Operating	-20° to +105°C

Wire/Cable Type	UL 1015
Wire Size (AWG)	16

This document was generated on Sep 24, 2025