

Specification Sheet

Part Number: 156-02700

Edge Clip applies easily to plastic and metal sheets without the need for a mounting hole.

Edge Clip provides low insertion force and high extraction force ideal for assembly environments.



Two piece assembly allows the mount to slide along the strap ensuring proper orientation.

Cable tie is outside serrated to reduce bundle chafing.

2-Piece Cable Tie with Edge Clip, 7.8" Long, 0.24 - 0.31" Panel, HS/HIRHS, Black, 500/pkg

Article Number 156-02700

Type T50ROSEC6-8

Color Black (BK)

Quantity Per pack

Product Description HellermannTyton's Two Piece Edge Clip with Cable Tie Assemblies are designed specifically to route bundles by securing them to the edge of a plastic or metal sheet without the need for a mounting hole. The clip is easy to secure and the extraction force is high due to the integrated metal clamp that holds the edge clip in place.

| | |
|-----------------------------------|---|
| Short Description | 2-Piece Cable Tie with Edge Clip, 7.8" Long, 0.24 - 0.31" Panel, HS/HIRHS, Black, 500/pkg |
| Global Part Name | T50ROSEC6-8-PA66HS/PA66HIRHS-BK |
| Minimum Tensile Strength (Metric) | 225 |
| Length L (Metric) | 200.0 |
| Fixation Method | Edge Clip |
| Identification Plate Position | none |
| Variant | Outside Serrated |
| Width W (Metric) | 4.6 |
| Bundle Diameter Min (Imperial) | 0.04 |
| Bundle Diameter Min (Metric) | 1.0 |
| Bundle Diameter Max (Imperial) | 1.77 |
| Bundle Diameter Max (Metric) | 45.0 |
| Height H (Metric) | 1.3 |
| Panel Thickness Min (Imperial) | 0.24 |
| Panel Thickness Max (Imperial) | 0.31 |
| Panel Thickness Min (Metric) | 6.0 |

| | |
|------------------------------|--|
| Panel Thickness Max (Metric) | 8.0 |
| Material | Polyamide 6.6, high impact modified, heat stabilized (PA66HIRHS) Polyamide 6.6 heat stabilized (PA66HS) |
| Foot Part Material | PA66HIRHS |
| Material Shortcut | PA66HS PA66HIRHS |
| Material Cable Tie | Polyamide 6.6 heat stabilized (PA66HS) |
| Flammability | UL 94 HB |
| UV Resistant (Yes/No) | No |
| Use Conditions | For Indoor and Outdoor Use |
| Operating Temperature | -40°F to +221°F (-40°C to +105°C) |
| Reach Compliant (Article 33) | Yes |
| ROHS Compliant | Yes |
| Package Quantity (Imperial) | 500 |
| Package Quantity (Metric) | 500 |
| Customs Number | 3926909988 |

7930 N. Faulkner Road, Milwaukee, WI 53224

Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2026 HellermannTyton. All Rights Reserved.

[Contact Us](#) [RoHS/WEEE Compliance](#) [Privacy Policy](#) [Cookie Policy](#) [Terms and Conditions](#)