Data sheet

H0,5/10

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com



For conductors from 0.25 to 6,0 mm² (AWG 24 - 10)
tin-plated copper
dimensional tolerances to DIN 46228 part 1
• supplied loose in polybag

General ordering data

Version	Wire-end ferrule, Standard, 10 mm, 10 mm, No
Order No.	9004050000
Type	H0,5/10
GTIN (EAN)	4008190153052
Qty.	1000 items
Packaging	loose

Downloaded from Arrow.com.

Data sheet

H0,5/10

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Technical data

Approvals

Approvals	
ROHS	Conform
UL File Number Search	UL Website
Certificate no. (cULus)	E499744

Dimensions and weights

Net weight	0.05 g

Environmental Product Compliance

RoHS Compliance Status	Compliant without exemption
REACH SVHC	No SVHC above 0.1 wt%

Technical data

Description of article	Wire end ferrule without plastic collar, (2)Wire-end ferrule	Version	Standard

Wire-end ferrules

Contact surface diameter (D1)	1 mm	Contact surface length (L2)	10 mm
Collar diameter (D2)	2.1 mm	L1 in mm	10.00 mm
Wire connection cross section AWG, max.	AWG 20	Stripping length	10 mm
Conductor cross-section	0.5 mm²		

Classifications


ETIM 8.0	EC000005	ETIM 9.0	EC000005
ETIM 10.0	EC000005	ECLASS 14.0	27-40-02-01
ECLASS 15.0	27-40-02-01		

Downloaded from Arrow.com.

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings



Downloaded from Arrow.com.