



Part Number : [1301080164](#)

Product Description : Super-Safeway Twin Tube 64W Fluorescent Work Light 16/3 SJOW Feed Thru 7.62m (25.0') Cord Length

Series Number : 130108

Status : Active

Product Category : Lamps and Lights

Engineering Number : 1351



Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Not Relevant

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
--------	--------

Category	Lamps and Lights
Series	130108
Description	Super-Safeway Twin Tube 64W Fluorescent Work Light 16/3 SJOW Feed Thru 7.62m (25.0') Cord Length
NEMA Configuration	NEMA 5-15
Product Family	Wide-Area Lighting Products
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678867150

Agency

UL	E174254
----	---------

Electrical

Lamp Wattage - Maximum	64W
Lumens	5700
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ

Physical

Bulb Type	Fluorescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	0.152m (6.00")
Cord Type - Primary	16/3 SJOW
Depth	190.75mm (7.510")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	82.55mm (3.250")
Lamp Type	F32/T8
Length	1.39m (54.620")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Adjustable Brackets

Outlet	Feed-Through
Packaging Type	Carton

This document was generated on Sep 11, 2023