

Amphenol Connex									
PART DESCRIPTION									
BNC JACK TO UHF JACK ADAPTER									
PART NO. 242165									
DWG. NO. 242165.DWG									
REV. A									
SIZE A									
SCALE NA									
APPROVALS		DATE							
DRAWN G.R.S.		01/22/04							
CHECKED									
ISSUED									
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:									
0.5 - .8mm ± 0.20mm									
.8 - .50mm ± 0.40mm									
.50 - .120mm ± 0.50mm									
UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:									
.020 - .315 = ± 0.007"									
.315 - 1.180 = ± 0.015"									
1.180 - 4.724 = ± 0.020"									
DO NOT SCALE DRAWING									
QTY		FINISH		MATERIAL		DESCRIPTION			
1		GOLD		BRASS		CONTACT PIN (UHF)			
1		GOLD		PHOS. BRONZE		CONTACT PIN (BNC)			
1		NATURAL		TEFLON		INSULATOR			
1		GOLD		BRASS		BODY			

