

H4,0/20D GR

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com



- supplied loose in polybag
- DIN colour code
- other colour code

General ordering data

Version	Wire-end ferrule, insulated, 14 mm, 12 mm, grey
Order No.	9019200000
Type	H4,0/20D GR
GTIN (EAN)	4008190126575
Qty.	500 pc(s).
Packaging	loose

Creation date November 25, 2020 6:16:04 PM CET

Catalogue status 20.11.2020 / We reserve the right to make technical changes.

H4,0/20D GR**Weidmüller Interface GmbH & Co. KG**

Klingenbergstraße 26

D-32758 Detmold

Germany

www.weidmueller.com

Technical data**Dimensions and weights**

Net weight	0.286 g
------------	---------

Technical data

Description of article	Wire end ferrule with plastic collar, grey	Version	insulated
------------------------	--	---------	-----------

Wire-end ferrules

Collar diameter (D2)	4.8 mm	Colour code	DIN
Conductor cross-section	4 mm ²	Contact surface diameter (D1)	2.8 mm
Contact surface length (L2)	12 mm	L1 in mm	20 mm
Metal sleeve thickness (S1)	0.2 mm	Military designation	T 20A 020 A
Plastic collar thickness (S2)	0.3 mm	Stripping length	14 mm
Wire connection cross section AWG, max.	AWG 12		

Classifications

ETIM 6.0	EC000005	ETIM 7.0	EC000005
eClass 9.0	27-40-02-01	eClass 9.1	27-40-02-01
eClass 10.0	27-40-02-01	eClass 11.0	27400201

Approvals

Approvals



ROHS	Conform
UL File Number Search	E499744

Downloads

Brochure/Catalogue	CAT 6 TOOLS 15/16 EN
Engineering Data	STEP
Engineering Data	EPLAN, WSCAD, Zuken E3.S
User Documentation	Technical information - EN Technical information - DE

H4,0/20D GR

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 26
D-32758 Detmold
Germany

www.weidmueller.com

Drawings

Drawing

