

6

5

4

3

2

1

APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	3/17/16	

D

D

C




C

B

B

A

A

**SPECIFICATIONS:**

Material:

Insulator: Nylon66, rated UL 94V-0

Insulator color: Beige

Electrical:

Voltage rating: 250 VAC/DC

Current rating: 1A AC/DC

Contact resistance: 10 mohms max

Insulation resistance: 1,000Mohms min

Dielectric withstanding voltage: 500 VAC for 1 minute

Temperature Rating:

Operating temperature: -25°C to +85°C

Environmental:

Lead free, RoHS compliant.



Positions: 2 thru 10, 11, 12, 14, 15, 20, 25, 30

A =.049 [1.25] X No. of Spaces

B =.049 [1.25] X No. of Spaces + .071 [1.80]

C =.049 [1.25] X No. of Spaces + .114 [2.90]

UNLESS OTHERWISE SPECIFIED
ALL DIMENSIONS ARE INCHES [MM]
TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

APPROVALS		DATE
DRAWN	HR	3/17/16
CHECKED	SC	3/17/16
APPROVED		

ADAM TECH

909 Rahway Avenue, Union, NJ 07083

Phone: 908-687-5000 Fax: 908-687-5710

TITLE
1.25mm CRIMP HOUSING SINGLE ROW
2 THRU 30 POSITIONS, COLOR: GRAY

SIZE	PART NO.	REV.
X	125CH-C1-XX	-
REF:	S00015T	SCALE: NTS
SHEET 1 OF 1		

6

5

4

3

2

1