

		1		2		3		4		5		6		7																																															
A		<div>RoHS & REACH Compliant</div>												Signature		Revision History		Date		Rev.																																									
														LIBRA		For Bulk Production		Mar. 05, 2018		01																																									
B																A																																													
C																C																																													
D		<div><div>Assignment</div><table><thead><tr><th colspan="2">Conn.1</th><th colspan="2">Conn.2</th></tr></thead><tbody><tr><td>1</td><td>Red</td><td>1</td><td></td></tr><tr><td>2</td><td>White</td><td>2</td><td></td></tr><tr><td>3</td><td>Green</td><td>3</td><td></td></tr><tr><td>4</td><td>Black</td><td>4</td><td></td></tr><tr><td>5</td><td>Blue</td><td>8</td><td></td></tr><tr><td>6</td><td>Yellow</td><td>9</td><td></td></tr><tr><td>7</td><td>Drain</td><td>7</td><td></td></tr><tr><td>8</td><td>Drain</td><td>5</td><td></td></tr><tr><td>9</td><td>Purple</td><td>6</td><td></td></tr><tr><td>Shell</td><td>Shield+Braid</td><td>Shell</td><td></td></tr></tbody></table></div>														Conn.1		Conn.2		1	Red	1		2	White	2		3	Green	3		4	Black	4		5	Blue	8		6	Yellow	9		7	Drain	7		8	Drain	5		9	Purple	6		Shell	Shield+Braid	Shell		D	
Conn.1		Conn.2																																																											
1	Red	1																																																											
2	White	2																																																											
3	Green	3																																																											
4	Black	4																																																											
5	Blue	8																																																											
6	Yellow	9																																																											
7	Drain	7																																																											
8	Drain	5																																																											
9	Purple	6																																																											
Shell	Shield+Braid	Shell																																																											
E		<div>NOTES:</div> <div>1. CABLE: UL2725 (28AWG*1P+EAM)*2C+(28AWG*1P+AL)+28AWG*2C+AEB (16/4/0.12MM 50%AL) OD:5.5MM Black PVC Mark: E342987 AWM STYLE 2725 80C 30V VW-1 SUPER HIGH SPEED USB Revision 3.0</div> <div>2. CONNECTOR: P1, P2:USB 3.0 AM~PBT Insulator Shell Nickel</div> <div>3. Shell: MOLDED TYPE, PVC 45P, COLOR:BLACK.</div> <div>4. Internal Molding transparent PE material.</div> <div>5. ELECTRICLE TEST: 1). 100% OPEN & SHORT & MIS WIRE TEST 2). CONTACT RESISTANCE:2 OHM(MAX) 3). INSULATION RESISTANCE:10M OHM(MIN) 4). HI-POT TEST:DC 300V/10ms</div>														E																																													
F		<div>Cross Section:</div>														F																																													
G		<table><thead><tr><th colspan="2"></th><th>Date</th><th>Name</th><th colspan="2">Part No.</th></tr></thead><tbody><tr><td>Drawn by</td><td></td><td>Mar. 05, 2018</td><td>Lyw</td><td colspan="2">AK-300114-010-S</td></tr><tr><td>Checked by</td><td></td><td>Mar. 05, 2018</td><td>Saul</td><td colspan="2">EAN:4016032283201</td></tr><tr><td>Approved by</td><td></td><td>21, Nov. 2018</td><td>Dachen China</td><td colspan="2">Title</td></tr><tr><td colspan="4" rowspan="3">ASSMANN Electronic GmbH</td><td colspan="2">USB3.0 Cable AM TO AM Black 1M</td></tr><tr><td>Scale</td><td>N/A</td></tr><tr><td>Unit</td><td>MM</td></tr><tr><td colspan="4"></td><td colspan="2">Sheet 1/2</td></tr></tbody></table>														Date	Name	Part No.		Drawn by		Mar. 05, 2018	Lyw	AK-300114-010-S		Checked by		Mar. 05, 2018	Saul	EAN:4016032283201		Approved by		21, Nov. 2018	Dachen China	Title		ASSMANN Electronic GmbH				USB3.0 Cable AM TO AM Black 1M		Scale	N/A	Unit	MM					Sheet 1/2		G							
		Date	Name	Part No.																																																									
Drawn by		Mar. 05, 2018	Lyw	AK-300114-010-S																																																									
Checked by		Mar. 05, 2018	Saul	EAN:4016032283201																																																									
Approved by		21, Nov. 2018	Dachen China	Title																																																									
ASSMANN Electronic GmbH				USB3.0 Cable AM TO AM Black 1M																																																									
				Scale	N/A																																																								
				Unit	MM																																																								
				Sheet 1/2																																																									
H														H																																															
		1		2		3		4		5		6		7																																															

	1	2	3	4	5	6	7																													
A	<h1>Package Details</h1> <div>RoHS & REACH Compliant</div>					<table border="1"> <tr> <td>Signature</td><td>Revision History</td><td>Date</td><td>Rev.</td></tr> <tr> <td>LIBRA</td><td>For Bulk Production</td><td>Mar. 05, 2018</td><td>01</td></tr> </table>		Signature	Revision History	Date	Rev.	LIBRA	For Bulk Production	Mar. 05, 2018	01	A																				
Signature						Revision History	Date	Rev.																												
LIBRA	For Bulk Production	Mar. 05, 2018	01																																	
B	Single Cable							B																												
C	<table border="1"> <thead> <tr> <th>P/N</th><th>Cable Length</th><th>Rolling Size (Single Cable)</th><th>Polybag Type (Single Cable)</th><th>Bag Size (Single Cable)</th><th>Article Weight (Single Cable)</th></tr> </thead> <tbody> <tr> <td>AK-300114-010-S</td><td>1m</td><td>mm max.</td><td>ednet Polybag (Stick type)</td><td>116*239*0.11MM</td><td>0.055 kg</td></tr> </tbody> </table>							P/N	Cable Length	Rolling Size (Single Cable)	Polybag Type (Single Cable)	Bag Size (Single Cable)	Article Weight (Single Cable)	AK-300114-010-S	1m	mm max.	ednet Polybag (Stick type)	116*239*0.11MM	0.055 kg	C																
P/N	Cable Length	Rolling Size (Single Cable)	Polybag Type (Single Cable)	Bag Size (Single Cable)	Article Weight (Single Cable)																															
AK-300114-010-S	1m	mm max.	ednet Polybag (Stick type)	116*239*0.11MM	0.055 kg																															
D	Inner Packing Unit							D																												
E	<table border="1"> <thead> <tr> <th>P/N</th><th>Cable Length</th><th>Quantity (Inner Packing Unit)</th><th>Type (Inner Packing Unit)</th><th>Size (Inner Packing Unit)</th><th>Weight (Inner Packing Unit)</th></tr> </thead> <tbody> <tr> <td>AK-300114-010-S</td><td>1m</td><td>10pcs</td><td>Polybag (Heat Sealed)</td><td>400*350*0.06MM</td><td>0.55 kg</td></tr> </tbody> </table>							P/N	Cable Length	Quantity (Inner Packing Unit)	Type (Inner Packing Unit)	Size (Inner Packing Unit)	Weight (Inner Packing Unit)	AK-300114-010-S	1m	10pcs	Polybag (Heat Sealed)	400*350*0.06MM	0.55 kg	E																
P/N	Cable Length	Quantity (Inner Packing Unit)	Type (Inner Packing Unit)	Size (Inner Packing Unit)	Weight (Inner Packing Unit)																															
AK-300114-010-S	1m	10pcs	Polybag (Heat Sealed)	400*350*0.06MM	0.55 kg																															
F	CARTON DETAILS							F																												
G	<table border="1"> <thead> <tr> <th>P/N</th><th>Cable Length</th><th>Quantity (Carton)</th><th>Measurement (Carton)</th><th>N.W. (Carton)</th><th>G.W. (Carton)</th></tr> </thead> <tbody> <tr> <td>AK-300114-010-S</td><td>1m</td><td>200pcs</td><td>430*430*250MM</td><td>11.0 kg</td><td>12.2 kg</td></tr> </tbody> </table>							P/N	Cable Length	Quantity (Carton)	Measurement (Carton)	N.W. (Carton)	G.W. (Carton)	AK-300114-010-S	1m	200pcs	430*430*250MM	11.0 kg	12.2 kg	G																
P/N	Cable Length	Quantity (Carton)	Measurement (Carton)	N.W. (Carton)	G.W. (Carton)																															
AK-300114-010-S	1m	200pcs	430*430*250MM	11.0 kg	12.2 kg																															
H	<p> EAN-Code: EAN-Code: </p> <p> * "ROTTERDAM" is for Sea Freight shipment * "COLOGNE" is for Air Freight shipment * "LUDENSCHIED" is for Fedex or UPS shipment </p>					<table border="1"> <tr> <td></td><td>Date</td><td>Name</td><td>Part No.</td></tr> <tr> <td>Drawn by</td><td>Mar. 05, 2018</td><td>Lyw</td><td>AK-300114-010-S</td></tr> <tr> <td>Checked by</td><td>Mar. 05, 2018</td><td>Saul</td><td>EAN: 4016032283201</td></tr> <tr> <td>Approved by</td><td>21, Nov. 2018</td><td>Dachen China</td><td></td></tr> <tr> <td colspan="3" rowspan="3"> ASSMANN Electronic GmbH </td><td>Title</td></tr> <tr> <td>USB3.0 Cable AM TO AM Black 1M</td></tr> <tr> <td> <table border="1"> <tr> <td>Scale</td><td>N/A</td><td>Sheet</td></tr> <tr> <td>Unit</td><td>MM</td><td>2/2</td></tr> </table> </td></tr> </table>			Date	Name	Part No.	Drawn by	Mar. 05, 2018	Lyw	AK-300114-010-S	Checked by	Mar. 05, 2018	Saul	EAN: 4016032283201	Approved by	21, Nov. 2018	Dachen China		ASSMANN Electronic GmbH			Title	USB3.0 Cable AM TO AM Black 1M	<table border="1"> <tr> <td>Scale</td><td>N/A</td><td>Sheet</td></tr> <tr> <td>Unit</td><td>MM</td><td>2/2</td></tr> </table>	Scale	N/A	Sheet	Unit	MM	2/2	H
	Date	Name	Part No.																																	
Drawn by	Mar. 05, 2018	Lyw	AK-300114-010-S																																	
Checked by	Mar. 05, 2018	Saul	EAN: 4016032283201																																	
Approved by	21, Nov. 2018	Dachen China																																		
ASSMANN Electronic GmbH			Title																																	
			USB3.0 Cable AM TO AM Black 1M																																	
			<table border="1"> <tr> <td>Scale</td><td>N/A</td><td>Sheet</td></tr> <tr> <td>Unit</td><td>MM</td><td>2/2</td></tr> </table>	Scale	N/A	Sheet	Unit	MM	2/2																											
Scale	N/A	Sheet																																		
Unit	MM	2/2																																		
	1	2	3	4	5	6	7																													