


Код: 206309

[Материнская плата s2011-в3 Intel C612I AN Supermicro MBD-X10DBH-CL N4-O]



Expansion Slots	
PCI-Express	• 2x PCI-E 3.0 x16 • 4x PCI-E 3.0 x8 • 1x PCI-E 3.0 x4 (in x8)
System BIOS	
BIOS Type	• 128Mb SPI Flash EEPROM with AMI BIOS
BIOS Features	• Plug and Play (PnP) • PCI 2.3 • ACPI 1.0 / 2.0 / 3.0 / 4.0 • USB Keyboard support • SMBIOS 2.7.1 • UEFI 2.3.1
Management	
Software	• Intel® Node Manager 3.0 • IPMI 2.0 • NMI • SPM • SSM • SUM • SuperDoctor® III • SuperDoctor® 5 • Watch Dog
Power Configurations	• ACPI / APM Power Management • Power-on mode for AC power recovery
PC Health Monitoring	
Voltage	• Monitors for CPU Cores, +1.8V, +3.3V, +5V, +12V, +3.3V Standby, +5V Standby, VBAT, Memory s, • 6 Phase-switching voltage regulator
FAN	• 8x 4-pin fan headers (up to 8 fans) • 8x fans with tachometer monitoring • Status monitor for speed control • Pulse Width Modulated (PWM) fan connectors
Temperature	• Monitoring for CPU and chassis environment • CPU thermal trip support • Thermal Control for 8x Fan Connectors • Thermal Monitor 2 (TM2) support • PECI
LED	• CPU / System Overheat • Suspend static indicator • UID/Remote UID
Other Features	• Chassis intrusion detection • Chassis intrusion header • SDDC Support • RoHS
Operating Environment	
Operating Temperature Range	• 10°C - 35°C (50°F - 95°F)
Non-Operating Temperature Range	• -40°C - 70°C (-40°F - 158°F)
Operating Relative Humidity Range	• 8% - 90% (non-condensing)
Non-Operating Relative Humidity Range	• 5% - 95% (non-condensing)
Parts List (Bulk)	
Parts List (Bulk)	• Part Number
Parts List (Single)	
Parts List (Single)	• Part Number
Optional Parts List	
Optional Parts List	• SuperDOM