

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080091](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Super-Safeway™ 4W Fluorescent Hand Lamp with Cord Ballast Location and no Switch, Cord Type 18/3 SJTW, Cord Length 5.49m (18.0')



Documents:
[RoHS Certificate of Compliance \(PDF\)](#) [Product Literature \(PDF\)](#)

Agency Certification	
CSA	LR85374
General	
Product Family	Portable Lighting
Series	130108
NEMA Configuration	NEMA 5-15
Outlet	None
Overview	Hand Lamps
Product Literature Order No	987650-8053
Product Name	Super-Safeway™
Type	Hand Lamps
UPC	78678861231
Woodhead	Yes
Physical	
Cord Length - Primary	5.49m (18.0')
Cord Length - Secondary	N/A
Depth	31.75mm (1.250")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	N/A
Length	342.90mm (13.500")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Hand Held
Packaging Type	Carton
Socket Construction	N/A
Electrical	
Bulb Type	Fluorescent
Cord Type - Primary	18/3 SJTW
Lamp Type	F4/T5
Lamp Wattage - Maximum	4W
Lumens	95
On/Off Switch	No
Voltage (Fixture) - Maximum	120VAC 60 HZ
Material Info	
Old Part Number	1045

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

China RoHS

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed

Search Parts in this Series

[130108](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION