

**Part Number :** [192050001](#)

**Product Description :** VersaKrimp Parallel Splice for 16-14 AWG Wire, Carton

**Series Number :** 19205

**Status :** Active

**Product Category :** Splices

**Engineering Part Number :** BS-304



---

## Documents and Resources

### Drawings

[192050001\\_sd.pdf](#)


### Specifications

[PS-19902-013-001.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Compliant with Exemption 44
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

### Part Details

#### General

Status	Active
Category	Splices
Series	19205
Description	VersaKrimp Parallel Splice for 16-14 AWG Wire, Carton
Product Name	VersaKrimp
Type	Parallel Splice
UPC	800755060829

#### Agency

CSA	LR18689
UL	E32244

#### Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Metal	Copper
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.488/g
Packaging Type	Carton
Wire Size (AWG)	14, 16

---

### Application Tooling

#### Global

Description	Part Number
-------------	-------------

Crimp Head for the AT-200 Pneumatic Hand Tool	<u>192820001</u>
Hand Crimp Tool	<u>192840001</u>
PremiumGrade Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 22-10 AWG and 6.0mm <sup>2</sup> - 0.5mm <sup>2</sup>	<u>640030100</u>
Crimp Head for the AT-200 Pneumatic Hand Tool	<u>640070100</u>
ServiceGrade Hand Crimp Tool - Ratchet	<u>640160038</u>

---

This document was generated on May 20, 2026