

Stainless Steel Cable Ties



Features


- Industry Standard Type 304 – Lock Ball Style – RoHS Compliant
- Maximum Temperature: +1472°F (+800°C)

Ideal Applications

- Harsh, Corrosive, and Salt-Water Environments, Chemical and Radiation Exposure, Food Processing and Vibrating Equipment



WT-08



100 lb. Stainless Steel

	NTE Type No.	Tensile Strength	Length	Width	Thickness	Max. Bundle Dia.	Qty. per Bag	Diag No.
NEW	04-06100SS	100 lb.	5.9 / 150	.180 / 4.6	.012 / .305	1.38 / 35.052	100	WT-08
NEW	04-09100SS	100 lb.	9.45 / 240	.180 / 4.6	.012 / .305	2.17 / 55.118	100	WT-08
NEW	04-14100SS	100 lb.	13.78 / 350	.180 / 4.6	.012 / .305	3.54 / 89.916	100	WT-08

150 lb. Stainless Steel

	NTE Type No.	Tensile Strength	Length	Width	Thickness	Max. Bundle Dia.	Qty. per Bag	Diag No.
NEW	04-06150SS	150 lb.	5.9 / 150	.315 / 8.0	.012 / .305	1.38 / 35.052	100	WT-08
NEW	04-09150SS	150 lb.	9.45 / 240	.315 / 8.0	.012 / .305	2.17 / 55.118	100	WT-08
NEW	04-12150SS	150 lb.	11.81 / 300	.315 / 8.0	.012 / .305	2.86 / 72.644	100	WT-08
NEW	04-14150SS	150 lb.	13.78 / 350	.315 / 8.0	.012 / .305	3.54 / 89.916	100	WT-08
NEW	04-20150SS	150 lb.	19.69 / 500	.315 / 8.0	.012 / .305	5.91 / 150.114	100	WT-08
NEW	04-24150SS	150 lb.	23.62 / 600	.315 / 8.0	.012 / .305	6.69 / 169.926	100	WT-08

250 lb. Stainless Steel

	NTE Type No.	Tensile Strength	Length	Width	Thickness	Max. Bundle Dia.	Qty. per Bag	Diag No.
NEW	04-08250SS	250 lb.	7.87 / 200	.455 / 13.0	.015 / .381	1.97 / 50.038	100	WT-08
NEW	04-14250SS	250 lb.	13.78 / 350	.455 / 13.0	.015 / .381	3.54 / 89.916	100	WT-08
NEW	04-20250SS	250 lb.	19.69 / 500	.455 / 13.0	.015 / .381	5.91 / 150.114	100	WT-08

Note 1. Dimensions are listed as "inch / millimeter".