HellermannTyton

Technical data sheet

Article number:
161-64204 **HWPP16L2**



Product Group	Helawrap cable cover
Product Family	HWPP in polypropylene
Material	Polypropylene (PP)
Colour	Black (BK)

Bundle Ø max.	16 mm
Bundle Ø min.	13 mm
Flammability	UL 94 HB
Nominal Ø	16 mm
Operating Temperature	-60 °C to +110 °C, intermittent +140 °C
Package Content	2 m
Package Content packed in	pack
Specifications	ECE R 118-03 Abschnitt 6
Wall (WT)	0.8 mm

HF ✓ RoHS ✓

ECE R-118

created on 31. July 2026, 4:00 am

Technical changes and errors reserved. It´s up to the customer to check the suitability for a specific application by means of tests.

Downloaded from Arrow.com.