



Catalog No. A18-8F

Description: NON-INS FORK TERM 22-16 No8

UPC No 786210803012

Home > Connectivity & Grounding > Sta-Kon > Electrical terminals

Non-Insulated Fork Terminal, Length 0.75 Inches, Width 0.31 Inches, Bolt Hole #8, Wire Range #22-16 AWG, Copper, Tin Plated, 100 Pieces

Descriptors	
Category	Electrical terminals
Special Features	These non-insulated fork terminals are made of electrolytic copper for high conductivity. They can be installed with crimping tools having a single indenter or double indenter (recommended for solid wire). Serrated barrel increases grip on wire.
Specifications	
Voltage Rating	600 V
Material	Copper
Color	Metallic
Classifications	
Brand Name	Sta-Kon
Standard	UL E9809 UL E9809
Dimensions	
Wire Size	22-16 AWG
Compliance and Certifications	
RoHS	RoHS3 Compliant
REACH	REACH 240 Compliant
TSCA	TSCA Section 6(h) Compliant
ETIM	EC001052 Solderless copper terminals for copper conductors
Flange shape	Fork shape
Insulation	None
Reel packaging	N
AWG-range	22-16

ETIM	EC001052 Solderless copper terminals for copper conductors
Material	Copper
Surface protection	Tinned
Stud size (imperial)	8