

+ SHIPS FREE
UPS FLAT RATE
MILITARY DISCOUNT
IBEW-NECA DISCOUNT

[Account](#) | [Wishlist](#) | [Quick Order](#) | [Log In](#)

 100% Lifetime Guarantee



Torx

Torque Tools

Tech Tools

Shop Tools

Screwdrivers

Pliers

Insulated

Hex

ESD Safe

Bits & Sets

Catalogs

[Best Sellers](#) [On Sale](#)

[Home](#) → [Tool Types](#) → [Screwdrivers](#) → [Insulated Hex Metric Screwdrivers](#)

Insulated Hex Metric Screwdrivers



Zoom

Titles and descriptions supersede the photo. We typically use the same image for different sizes of tools.

[Be the first to review this product](#)

Filter:

SKU	Product	Size Hex Metric	Blade Length MM	OAL MM	Blade Length Inch	OAL Inch	Price	Qty
32302	Insulated Hex Metric Driver 2.5 x 75mm	2.5mm	75	179	3	7		0 
32303	Insulated Hex Metric Driver 3.0 x 75mm	3.0mm	75	179	3	7		0 
32304	Insulated Hex Metric Driver 4.0 x 75mm	4.0mm	75	186	3	7.3		0 
32305	Insulated Hex Metric Driver 5.0 x 75mm	5.0mm	75	186	3	7.3		0 
32306	Insulated Hex Metric Driver 6.0 x 100mm	6.0mm	100	218	3.9	8.6		0 
32308	Insulated Hex Metric Driver 8.0 x 100mm	8.0mm	100	218	3.9	8.6		0 

Add to Cart

[Add to Wishlist](#)[Share on Facebook](#)[Tweet This](#)[Pin it](#)

We accept



Details

Meets ASTM F1505, VDE 0682/part201, DIN 7437, EN/IEC 60900, NFPA-70E & CSA specification

10,000 Volt Tested for a 1,000(AC) 1,500(DC) Volt Certification, VDE and GS tested

Ergonomic Wiha SoftFinish multi-component handle with roll-off protection

Cushioned Grip For maximum comfort and power

Perfect fit for your Hand because of Wiha handle size concept

Wiha special chrome-vanadium-molybdenum tool steel

Through hardened for best wear resistance

Precision machined exact fit Black tips

Precision machine chamfered ends

No cut off burrs or impact distortions

Additional Info

Head Type

  hex metric

Country of Manufacture

Germany

Handle Grip Types

Insulated

WRITE YOUR OWN REVIEW

Only registered users can write reviews. Please, [log in](#) or [register](#)

Warranty Info

Wiha Products Carry a **100% Satisfaction Guarantee**. All Wiha tools are guaranteed to be free of defects in workmanship and materials and will be replaced if found to be deficient providing tools have not been altered or misused. Wiha Insert Bits, Power Bits, Ceramic Tools and Tweezers are not warranted for use. Wiha Brand Torque control Tools are warranted for twelve months from date of purchase up to 5,000 torque Cycles.

[View Full Warranty](#)

You may also be interested in the following product(s)



Insulated Combination Terminal

Block Xeno Screwdrivers

★★★★★ 1 REVIEW(S)

Wiha Professional Quality Hand Tools

Wiha Tools USA Since 1985

Wiha Activities In the USA Started in August of 1985 bringing Wiha quality to professional tool

Wiha Tools USA Willi Hahn Corporation

A Subsidiary of [Wiha Werkzeuge Gmbh Schonach](#)



We produce Wiha products around the world under strict ISO quality standards. State of the art technology and special tool steels assure products consistent

users in North America. Our USA warehouse and distribution center services all 50 states & Our New Facilities In Canada Supply millions of tools from stock to professional quality conscious tool users throughout North America.

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

[Having technical issues with the website?](#)

We accept

[Germany](#)

**Monday - Friday Office Hours 7am - 5pm CST
USA**

1348 Dundas Cir,
Monticello, MN 55362

Customer Service Email: cservice@wihatools.com

Tel: [763-295-6591](tel:763-295-6591)

Fax: 763-295-6598

[Shipping](#)

[Returns](#)

[Warranty Info](#)

[About Us](#)

[Privacy Policy](#)

[Terms and Conditions](#)

**Over 5000 Professional Quality Wiha Tools In
Stock**



Newsletter

[Subscribe](#)