

DisplayPort 1.2 to HDMI Active Adapter Cable (M/M), 4K 60 Hz, Gripping HDMI Plug, HDCP 2.2, 3 ft. (0.9 m)

MODEL NUMBER: **P582-003-HD-V2A**



HDCP 2.2-compliant cable connects the DisplayPort output on your PC or Mac to a 4K-enabled HDMI monitor, projector or television.

Features

Send UHD DisplayPort 1.2a Signals to a 4K HDMI Display Connects DisplayPort PC or Mac to a 4K-enabled HDMI monitor, projector or HDTV Recommended for displaying video on a large monitor or digital sign DisplayPort and high-grip HDMI male connectors No separate power adapter required

Vibrant Video Quality Supports UHD video resolutions up to 4K @ 60 Hz (3840 x 2160), as specified in HDMI 2.0 Supports HDCP 2.2, audio and EDID Active adapter compatible with Single-Mode and Dual-Mode (DP++) DisplayPort output Recommended for graphics cards, such as AMD Eyefinity, that don't output DP++ signals.

Superior Materials for Superior Performance Gold-plated HDMI connector and contacts for maximum conductivity and minimum data loss Special high-grip HDMI plug prevents accidental disconnections Integral strain relief provides cable and connectors with flexibility and reduces stress

Highlights

- Supports video resolutions up to 4K @ 60 Hz (3840 x 2160)
- Compliant with latest HDCP 2.2 standards
- No separate power adapter required
- High-grip HDMI plug prevents accidental disconnections

Package Includes

- P582-003-HD-V2A DisplayPort 1.2a to HDMI Active Adapter Cable (M/M), 3 ft.

Specifications

OVERVIEW	
UPC Code	037332200723
Product Type	Active Cable
Technology	HDMI; DisplayPort
Cable Type	Active
VIDEO	
Max Supported Video Resolution	3840 x 2160 (4K) @ 60Hz



Powering Business Worldwide

TRIPP LITE
SERIES

CONNECTIONS	
Side A - Connector 1	DISPLAYPORT (MALE)
Side B - Connector 1	HDMI (MALE)
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Jacket Material	PVC
Cable Jacket Rating	VW-1
Cable Length (ft.)	3
Cable Length (m)	0.91
Cable Length (in.)	36
Shipping Dimensions (hwd / in.)	0.50 x 7.00 x 9.00
Shipping Dimensions (hwd / cm)	1.27 x 17.78 x 22.86
Shipping Weight (lbs.)	0.70
Shipping Weight (kg)	0.32
STANDARDS & COMPLIANCE	
Product Compliance	CE (Europe); FCC (USA); REACH; RoHS; UKCA; WEEE
WARRANTY & SUPPORT	
Product Warranty Period (Worldwide)	3-year limited warranty

1000 Eaton Boulevard
Cleveland, OH 44122
United States
<https://tripplite.eaton.com>

© 2025 Eaton. All Rights Reserved.
Eaton is a registered trademark. All other trademarks
are the property of their respective owners.