

## Detachable PDU option with IEC output connections for compatible SmartOnline UPS Systems

MODEL NUMBER: **SUPDMB710IEC**



### Description

The SUPDMB710IEC converts the output of our SmartOnline SU8000RT3U and SU10000RT3U to worldwide output connections. Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs. Can accept input voltages of 200-240 VAC. Hardwire input/ 6 IEC320 C19 output connections.

### Features

- Converts the output of our SmartOnline SU8000RT3U and SU10000RT3U to worldwide output connections
- Manual bypass feature ensures maximum availability of connected equipment while UPS maintenance occurs
- Can accept input voltages of 200-240 VAC
- Hardwire input/ 6 IEC320 C19 output connections

## Specifications

OVERVIEW	
UPC Code	037332143594
INPUT	
Nominal Input Voltage(s) Supported	200V AC; 208V AC; 230V AC; 240V AC; 220V AC
Input Connection Type	Hardwire

### Highlights

- Converts compatible SmartOnline high-voltage UPS systems to provide worldwide compatible output connections
- For use with input voltages of 200-240 VAC
- Hardwired input/ 6 IEC320 C19 output connections
- Manual bypass feature ensures maximum equipment availability

### System Requirements

- For use with SmartOnline SU8000RT3U and SU10000RT3U Rack/Tower UPS systems in applications requiring a detachable PDU with manual bypass

### Package Includes

- SUPDMB710IEC detachable PDU
- Mounting hardware
- Owner's Manual with warranty instructions



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Voltage Compatibility (VAC)	200; 208; 220; 230; 240
<b>OUTPUT</b>	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) C19
Output Nominal Voltage	200/208/220/230/240 VAC
Overload Protection	6 double-pole 20A circuit breakers
<b>PHYSICAL</b>	
Material of Construction	Sheet metal
Shipping Dimensions (hwd / cm)	34.04 x 23.88 x 24.38
Shipping Dimensions (hwd / in.)	13.40 x 9.40 x 9.60
Shipping Weight (kg)	4.49
Shipping Weight (lbs.)	9.90
Unit Dimensions (hwd / cm)	26 x 19.1 x 16.5
Unit Dimensions (hwd / in.)	10.25 x 7.5 x 6.5
Unit Weight (kg)	3.58
Unit Weight (lbs.)	7.9
<b>STANDARDS &amp; COMPLIANCE</b>	
Certifications	Tested to UL1778 (USA), CSA (Canada), CE (Europe)
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	2-year limited warranty

© 2020 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>