



Powering Business Worldwide

pe.eaton.com

Eaton Bussmann series EuroMag EM2575 terminal block

EM257508VC-BK

UPC:051712906272

Dimensions:

- **Height:** .504 IN
- **Length:** 1.6 IN
- **Width:** .472 IN

Weight: .1 LB

Warranties:

- Eaton Selling Policy 25-000 generally applies with some exceptions. Drive products come with a standard 24 months from date of shipment and 36 months with Eaton certified start up all inclusive coverage parts labor and travel.

Specifications:

- **Application:** industrial
- **Type:** Depluggable block
- **Voltage Rating:** 300 V
- **Number Of Poles:** Eight-pole
- **Operating Temperature:** -40° to 105°C
- **Wire Size:** #22-12 AWG Cu
- **Torque Rating:** 4.5 lb-in
- **Center Spacing:** 0.200 in
- **Recommended PCB Hole Diameter:** 0.055" (1.40mm)
- **Contact Material:** Tin plated brass
- **Housing Material:** UL rated 94V0 thermoplastic
- **Orientation:** Vertical
- **Material:** Tin-plated brass
- **Connection:** M3 X 5 screw

Supporting documents:



- [Product Catalog](#)

Certifications:

- UL Recognized

Product compliance:

- CE Marked
- RoHS Compliant
- EU Directive 2002/95/EC Category 3 (4 of 5)

© 2016 Eaton. All rights reserved.