Hello, We use cookies to create the most secure and effective website possible. By using this site, you consent to the use of cookies. See full details in our Privacy Statement.

Click here to not show this message again

14CE1-AQ

Overview



MICRO SWITCH 14CE Series Compact Precision Limit Switches, Top Plunger, 1NC 1NO SPDT Snap Action, 4-Pin dc Micro-Connector. ...

View More

view all 14CE1-AQ literature
view distributor inventory
sample request
email support
get support
email sales
find a distributor
email this page

Technical Specifications

Availability	Europe; Asia-Pacific
Release Force	4,4 N [0.99 lb] max.
Overtravel (OT)	3,0 mm [0.118 in] min.
Product Type	MICRO SWITCH Miniature Limit Switches
Termination Type	4-Pin dc Micro-Connector

Operating Force (OF)	11,8 N [2.65 lb] max.
Pretravel (PT)	1,0 mm ±0,5 mm [0.04 in ±0.02 in]
Differential Travel (DT)	0,1 mm [0.004 in] max.
Actuator	Top Plunger
Circuitry	1NC 1NO SPDT Snap Action

View More

View documents in: English

Documents

TITLE	DOCUMENT TYPE	LANGUAGE	SIZE
MICRO SWITCH 14CE Series Compact Limit Switches	Datasheet	English	6MB
XP-4040: 14CE/914CE Series Miniature Limit Switches with UL, CSA and CE approvals	Installation Instructions	English	151KB
MICRO SWITCH Limit Switches Comparison	Product Range Guide	English	460KB
Limit Switches and Machine Safety Range Guide	Product Range Guide	English	22MB

View More

Product Features

- Compact construction
- Pre-wired or connector versions
- Die-cast zinc housing
- Wide selection of actuators
- Gang mounting capability
- Cable length variations

Downloaded from Arrow.com.

- Side and bottom exit cable/connector
- Simple two-screw mounting
- Low temperature variants
- Fluorocarbon sealing (standard)

Applications

- Processing Equipment
- Textile Machinery
- Machine Tools
- Robotics
- Packaging Equipment
- Farm Machinery
- Commercial Laundry Equipment
- Printing Trade Machinery
- Vehicles

COPYRIGHT © 2018 HONEYWELL INTERNATIONAL INC.

Downloaded from Arrow.com.