


4611110026056



规格 Specifications


1. 相数 Number of Phase	2
2. 步距角 Step Angle	0.9°
3. 额定电压 Rated Voltage	3.56V DC
4. 额定电流 Rated Current	2.2Amp
5. 保持转矩 Holding Torque	1.5Nm Typ. (Two phase on/rated current)
6. 相电阻 Phase Resistance	1.62ohm $\pm$ 10%(20°C)
7. 相电感 Phase Inductance	10.5mH $\pm$ 20%(1kHz 1V rms)
8. 转子惯量 Rotor Inertia	220gcm ²
9. 电机重量 Motor Weight	0.6kg
10. 绝缘等级 Insulation Class	B (130°C)

带轮规格 Pulley Specification

齿型 Profile	MXL
齿数 Number of teeth	20
节距 Pitch	2.032
节圆 Pitch diameter	$\varnothing 12.94$
齿顶 Outside diameter	$\varnothing 12.43_0^{+0.05}$
材料 Material	HPb59-1

Housing: JST XHP-4
Terminal: JST SXH-001T-P0.6 4321 — PIN No.

接线图 Wiring Diagram



励磁顺序 vs. 旋转方向

Exciting Sequence vs. Direction of Rotation

STEP	A	B	C	D
1	+	+	-	-
2	-	+	+	-
3	-	-	+	+
4	+	-	-	+

从安装面看为顺时针方向

Clockwise view from mounting side

铭牌 Label Detail

MOONS' STEPPING MOTOR
TYPE MS23HA8L4220-02
XXXXXXX YY/MM/DD

Work Order 加工单号
Date Format 日期格式

备注 Comment:

1: 后盖密封垫增加 698151100075 绝缘垫片

(Add 3698151100075 Insulating gaskets to the back end cover cavity)

2: 轴承油温范围 40~150℃

(Bearing grease temperature tolerance range - 40 ~150℃)

Unit: mm
第一角画法
FIRST ANGLE METHOD
未注公差与尺寸公差
To be noted tolerance and angular dimensions without individual tolerance indication
GB/T 1804-2000 eqv ISO 2768-1 C
未注公差与尺寸公差
To be noted tolerance and angular dimensions without individual tolerance indication
GB/T 1184-K eqv ISO 2768-2 K

批准 Approve

标准 Standard

工艺 Technology

审核 Check

设计 Design

MOONS'

Shanghai Moons' Electric Co., Ltd.

This document is released for information only. Its reproduction in whole or in part or its dissemination to third parties is prohibited. All trademarks and registered trademarks appearing on this document are the property of their respective owners.

Type: MS23HA8L4220-02 Rev.E

SCALE 1:1 Sheet 1 of 1

6 7 8