

ENCLOSURE HARDWARE

LED INDICATORS

LIGHT PIPE SELECTOR

LED MOUNTS, HOLDERS

LEDs

LIGHT PIPES

BOARD MOUNT LED ASSEMBLIES

PANEL MOUNT LED ASSEMBLIES

LED LIGHTING

SOLUTIONS

RESOURCES

FLPR12.0-UG



Flexible Light Pipe Assembly, 1mm. Fiber Optic Core, Right Angle, 4.2mm. Dia. Low Profile Lens, 12.0in. Length, 3mm LED, Ultra Green



Datasheet



3D Model



Request Samples



RoHS Docs

FEATURES

VALUE ADDED

CHECK STOCK

- Wavelength: 570nm, Typical Intensity: 200mcd, Color: Green
- Assembly Includes Flexible Light Pipe, Right Angle Through-Hole Adaptor and LED
- 4.2mm. Diameter Low Profile Lens Cap
- Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info
- Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear
- Front Panel Mount Lens



Enclosure Hardware  
LED Indicators  
LED Lighting

New Products  
Locate a Distributor / Sales REP  
Quality Assurance / RoHS

Product Info Center  
Terms & Conditions  
My Bivar



100% Employee Owned