




HEX/Allen screw

Screw thread

view of the hood without lid

Cable diameter without rubber bushing:
ØF min: 3 mm
ØF max: 8.5 mm

Cable diameter with rubber bushing:
ØF max: 8 mm

Cable diameter without reduction plate:
ØF max: 12,5 mm

		All rights reserved Department EC PD - FR		HARTING Electronics GmbH D-32339 Espelkamp				All Dimensions in mm Original Size DIN A4		Scale 1:1		Free size tol.		Ref.			
						Sub.											
		Department EC PD - FR		HARTING Electronics GmbH D-32339 Espelkamp		Created by DOUGE		Inspected by BAGDIKIAN		Standardisation HOFFMANN		Date 2014-02-14		State Final Release			
						Title D-Sub 25-poles metal hood side entry										Doc-Key / ECM-Nr. 100567681/UGD/001/A 500000071307	
		Department EC PD - FR		HARTING Electronics GmbH D-32339 Espelkamp		Type TB		Number 09670250339						Rev. A		Page 1/1	

09670250339	M3
Part number	Screw thread