



**Part Number :** [1301430084](#)

**Product Description :** Super-Safeway Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 7.62m (25.0'), NEMA 5-20 125V

**Series Number :** 130143

**Status :** Active

**Product Category :** Wiring Devices

**Engineering Part Number :** 1433A123




---

## Documents and Resources

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	 per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Not Reviewed per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

## Part Details

### General

Status	Active
Category	Wiring Devices
Series	130143
Description	Super-Safeway Cordset 12 Gauge SOOW, 2 Pole/3 Wire, Cordset Length 7.62m (25.0'), NEMA 5-20 125V
IP Rating	N/A
NEMA Configuration	NEMA 5-20
Product Name	Super-Safeway
Specialty	N/A
Type	Cordset
UPC	78678870135

### Agency

CSA	LR6837
UL	E38085

### Electrical

Current - Maximum per Contact	20.0A
GFCI	No
Voltage - Maximum	125V

### Physical

Cord Type	12/3 SOOW
Flange	No
Flip Lid	No
Gender	Male-Female
Length	7.62m (25.0')
Lighted Connector	No
Locking Blade	No

Net Weight	1.000/g
Poles	2-pole/3-wire
Receptacle Type	Single

---

This document was generated on Jun 01, 2026