




- Protection level: IP67
- Temperature range: -25°C ... +80°C

length in "1m" step	100	XXX=000
	99	XXX=990
	.	.
	.	.
length in "0.1m" step	12	XXX=120
	11	XXX=110
	10	XXX=100
	9.9	XXX=099
	9.8	XXX=098
	.	.
	.	.
	.	.
	0.4	XXX=004
	0.3	XXX=003
	0.2	XXX=002
	0.1	XXX=001
Step	a [m]	XXX

4.0 to 100	+1%
0.1 to 3.9	+0.04
a [m]	Tolerance

Part no.	213499004XXXXX
----------	----------------

Type of cable	XX
PVC grey, 4x1.5mm ²	XX=95
PUR black, 4x1.5mm ²	XX=96

		All Dimensions in mm Original Size DIN A3		Scale 1.5:1		Free size tol.		Ref.							
								Sub.							
		All rights reserved Department EC PD - RO		Created by TAMAS		Inspected by AVRAM		Standardisation HOFFMANN		Date 2014-07-01		State Final Release			
				Title 7/8 Cable Assembly								Doc-Key / ECM-Nr. 100580928/UGD/009/A 500000076597			
HARTING Electronics GmbH D-32339 Espelkamp				Type TB		Number 213499004XXXXX						Rev. A		Page 1/1	