


REV.	DATE	DESCRIPTION
NC	01/02/07	INITIAL RELEASE



8					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
7						DRAWN	G.R.S.						01/02/07
6						CHECKED			PART DESCRIPTION 1.0/2.3 PCB RECEPTACLE – 75ohm				
5						ISSUED							
4						SHEET	1 OF 1						
3	CONTACT PIN	BER. COPPER	GOLD	1		PART NO. 282120–75							
2	INSULATOR	TEFLON	NATURAL	1									
1	BODY	BRASS	GOLD	1									
	DESCRIPTION	MATERIAL	FINISH	QTY		CAD FILE C:/282/282120–75.DWG			DWG. NO. 282120–75.DWG	REV. A	SIZE A	SCALE NA	