

Intel® Pentium® 4 Processor
(Socket 478)
CPU Cooler

SAN ACE MC



General Specifications

- Material Frame: Plastics (Flammability: UL94V-0),
Impeller: Plastics (Flammability: UL94V-1) Heatsink: Aluminum
- Lead Wire ⊕yellow (Connector No.2 side) ⊖black (Connector No.1 side)
Sensor green (Connector No.3 side)
- Connector Molex 22-01-3037: P/N 2695-03RP
- Contact Molex P/N 5159PBT or equivalent
- Mass 390g

Specifications

Model No.	Rated Voltage [V]	Operating Voltage Range [V]	Rated Current [A]	Rated Speed [min ⁻¹]	θ c-a Thermal Resistance [K/W]	SPL [dB(A)]	Operating Temperature [°C]	Life Expectancy [h]
109X9812T0H016	12	9 to 13.8	0.21	3,900	0.42	39	0 to +60	40,000
109X9812H0016		7 to 13.8	0.21	2,600	0.49	26		
				3,900	0.42	39		

Dimensions (Unit : mm)

