



NC4FX-HD

PHASE OUT

direct replacement / successor: NC4FXX-HD-D

alternative product: NC4FX-TOP

4 pole female cable connector, "heavy duty", all metal design, gold contacts

The X-HD Series is a "Heavy duty" XLR cable connector for outdoor use. All metal design, dust and water protected according to IP 65 by mating with related X-HD cable connector or MPR-HD chassis connector. Gold contacts are standard.

Features & Benefits

- ✓ "Heavy duty" cable connector for outdoor use
- ✓ All metal design
- ✓ NC*FX-HD mates with NC*MPR-HD chassis connector and NC*MX-HD cable connector
- ✓ Dust and water protected according IP 65 in mated condition
- ✓ Gold contacts
- ✓ Chuck type strain relief system for secure clamping of cables
- ✓ Boot with rubber gland gives high protection against bending stresses

Technical Information

Product	
Title	NC4FX-HD
Connection Type	XLR
Gender	female

Electrical	
Capacitance between contacts	≤ 7 pF
Contact resistance	≤ 3 mΩ
Dielectric strength	1,5 kVdc
Insulation resistance	> 10 GΩ (initial)
Rated current per contact	10 A
Rated voltage	< 50 V

Mechanical	
Cable O.D.	3.5 - 8.0 mm
Insertion force	≤ 20 N
Withdrawal force	≤ 20 N
Lifetime	> 1000 mating cycles
Wiresize	max. 1.5 mm²
Wiresize	max. 16 AWG
Wiring	Solder contacts
Locking device	Latch lock

Material	
Boot	Polyurethan
Bushing	Stainless steel
Contact plating	0.2 µm Au hard alloy over 2 µm Ni
Contacts	Brass (CuZn39Pb3)
Insert	Polyamide (PA66)
Locking element	St3K32 (latch) / Ck 67 (spring)
Shell	Stainless steel
Shell plating	Nickel
Strain relief	Polyacetal (POM)

Environmental	
Approvals	UL
Flammability	UL 94 V-0
Standard compliance	IEC 61076-2-103
Protection class	IP 65
Solderability	Complies with IEC 68-2-20
Temperature range	-30 °C to +80 °C