



Flexible Light Pipe Assembly, 1mm. Fiber Optic Core, Vertical, 7mm. Low Profile Dia. Lens, 6.0in. Length, 3mm LED, Super Bi-Color Red/Green



Datasheet



3D Model



Request Samples



RoHS Docs

FEATURES	VALUE ADDED	CHECK STOCK
<ul style="list-style-type: none">• Wavelength: 645nm / 568nm , Typical Intensity: 100mcd / 60mcd, Color: Red / Green• Assembly Includes Flexible Light Pipe, Vertical Through-Hole Adaptor and LED• 7mm. Diameter Low Profile Lens Cap• Flexible Light Pipe Cable Customized Length-See Specification Sheet for More Info• Material: Flexible Light Pipe Adaptor- Nylon 6/6 94V-0, Lens Cap- Polycarbonate 94V-0 Clear• Front Panel Mount Lens		

