

Aptiv Connection Systems Catalog

[Customer Service](#) [Samples Request](#)

[Find by Feature](#) [Browse by Category](#) [Browse by Application](#)

[Comparison List \(0\)](#) [Share](#)

Enter part number or keyword

[Search Results \(1\)](#) [Search Options](#)

1 Result(s): [All] - 10757258

[Compare](#)

211CC2S2230 - Sicma2 1.5 Female Unsealed Gold Plating Terminal, Cable Range 1.00 - 2.00 mm2

[Compare](#)

Sicma2 1.5 Female Unsealed Gold Plating Terminal, Cable Range 1.00 - 2.00 mm2

Part # 211CC2S2230



[Question about this product?](#)

[Attributes](#) [Documents \(1\)](#)

Part # :	211CC2S2230
Description :	Sicma2 1.5 Female Unsealed Gold Plating Terminal, Cable Range 1.00 - 2.00 mm2
Product Type :	Terminal
Status :	Active
Blade size [mm] :	1.5
Series :	1.5
Gender :	Female
Sealable :	Sealed
Material :	CuMg
Weight [g] :	2
Plating :	Gold
Maximum Cable Diameter [mm] :	2.60
Minimum Cable Core Cross Section [mm2] :	1.30
Maximum Cable Core Cross Section [mm2] :	2.00
Remarks :	Former FCI Product, Delphi PN:10757258,SICMA 2, One piece construction, High current carrying capacity, Low contact mating force, Class 4, temperature C, Suitable for secondary lock, Gold Plated

Certain products listed on this website may be subject to restricted usage or distribution or may not be available. For additional information, please contact your local sales office.