


REV.	DATE	DESCRIPTION
A	03/27/05	UPDATE DRAWING FORMAT



NOTES:

1. CRIMPED FERRULE
HEX CRIMP SIZE .128"
2. MAX. PANEL THICKNESS = 2.4mm

8				UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.60mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex				
7	HEAT SHRINK TUBE		1		DRAWN	G.R.S.					03/27/05
6	HEX NUT	BRASS	GOLD		1	CHECKED		PART NO. 152105			
5	LOCK WASHER	BRASS	GOLD		1	ISSUED					
4	FERRULE	COPPER	GOLD		1	SHEET	1 OF 1				
3	CONTACT PIN	BRASS	GOLD		1						
2	INSULATOR	TEFLON	NATURAL		1						
1	BODY	BRASS	GOLD		1						
	DESCRIPTION	MATERIAL	FINISH	QTY	CAD FILE C:/152/152105.DWG						