





APPROVED: _____

DATE: _____ TITLE: _____

Rev	AWO #	Description	Date	Appr
-		RELEASED	11/26/14	
A		UPDATE DRAWING	5/15/15	AY
B		UPDATE DRAWING	7/10/23	LH/LX



Circuit 1 2X07~2X22P



2X02~2X06P

SPECIFICATIONS:

Material:

Insulator: Nylon 66, rated UL 94V-0

Insulator color: White

Electrical:

Voltage rating: 250 VAC max

Current rating: 3 Amp AC/DC

Contact resistance: 10 mohms max

Insulation resistance: 1,000 Mohms min

Dielectric withstanding voltage: 800 VAC for 1 minute

Temperature Rating:

-25°C to +85°C

Environmental:

Lead free, RoHS compliant



Positions: 04 thru 44

A = .079 [2.00] x No. of Spaces

B = .079 [2.00] x No. of Spaces + .154 [3.90]

UNLESS OTHERWISE SPECIFIED ALL DIMENSIONS
ARE INCHES [MM]. TOLERANCES: EXCEPT AS NOTED

INCHES	HOLES
.X ± .10	Ø.X ± .10
.XX ± .020	Ø.XX ± .015
.XXX ± .015	Ø.XXX ± .010

DRAWN	AY	11/26/14
CHECKED	TW	11/26/14
APPROVED		

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY
AND SHOULD NOT BE USED WITHOUT PRIOR WRITTEN
PERMISSION FROM ADAM TECH

ADAM
TECH

909 Rahway Avenue,
Union, NJ 07083
Phone: 908-687-5000
Fax: 908-687-5710

TITLE				
.079 [2.00] PITCH HOUSING				
SIZE	PART NO.			REV.
X	2CHD-D-XX			-
REF:	S00186T	SCALE:	NTS	SHEET 1 OF 1