



Part Number : [638281700](#)
Product Description : Hand Crimp Tool for
Standard .093" Pin and Socket Crimp Terminals, 20
AWG
Series Number : 207129
Status : Active
Product Category : Crimp Presses and Crimp Hand
Tools



Documents & Resources

Tooling Specifications
[638281700-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2025)4165-DC (25 June 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

[EU RoHS Certificate of Compliance](#)
[Additional Product Compliance Information](#)

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, 20 AWG
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Standard .093"
Tool Type	Hand Crimp Tool
UPC	191130136728
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Applicable Parts

Description	Part Number
2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1381, Female, with Tin (Sn) Plated Brass Contact, 22-18 AWG, Reel	<u>02091117</u>
2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1381, Female, with Tin (Sn) Plated Brass Contact, 22-18 AWG, Bag	<u>02091119</u>
2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Tin (Sn) Plated Brass Contact, 22-18 AWG, Reel	<u>02092116</u>
2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Tin (Sn) Plated Brass Contact, 22-18 AWG, Bag	<u>02092118</u>
2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1381, Female, with Gold (Au) Plated Brass Contact, 22-18 AWG, Bag	<u>02095142</u>
2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1381, Female, with Gold (Au) Plated Brass Contact, 22-18 AWG, Reel	<u>02095143</u>
2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Gold (Au) Plated Brass Contact, 22-18 AWG, Reel	<u>02096122</u>
2.36mm Diameter, Standard .093" Pin and Socket Crimp Terminal, Series 1380, Male, with Gold (Au) Plated Brass Contact, 22-18 AWG,	<u>02096123</u>

Bag	
-----	--

This document was generated on Sep 10, 2025