

Product data sheet

Specifications



Condenser, 38kW, 95F(35C),208-230V/3, 60Hz

ACCD75228

Overview

Lead time	Special Order - Call for Quoted Lead Times
-----------	--

General

Air discharge option	Horizontal Upflow
Air flow	7868.31 l/s
Inrush current	10 A

Physical

Length	3.15 m
Depth	315.1 cm
Height	82.4 cm
Net weight	217.72 kg
Width	97.7 cm

Input

Minimum circuit ampacity	12 A
Network frequency	60 Hz
Maximum overcurrent protection	15 A
Input voltage	200 V 3 phases 208 V 3 phases 220 V 3 phases 240 V 3 phases

Conformance

Product certifications	ETL
------------------------	-----

Environmental

Ambient air temperature for operation	-20...50 °C
Operating altitude	0...10000 ft
Audible noise at 1 meter from surface of unit	65 dBA

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Packing Units

Package 1 Weight	272.16 kg
Package 1 Height	88.9 cm
Package 1 width	109.2 cm
Package 1 Length	330.2 cm

Offer Sustainability

Sustainable offer status	Green Premium product
REACH Regulation	REACH Declaration
REACH free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Lead free	Yes
California proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov

Contractual warranty

Warranty	1 year (parts only)
----------	---------------------