**Part Number :** 191930345
**Product Description :** VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton
**Series Number :** 19193
**Status :** Active
**Product Category :** Ring and Spade Terminals
**Engineering Part Number :** J-385-38



## Documents and Resources

### Drawings

191930345_sd.pdf

### Specifications

PS-19902-013-001.pdf

## Product Environment Compliance

### Compliance

| | |
|---|---|
| GADSL/IMDS | Compliant with Exemption 44 |
| China RoHS | per SJ/T 11365-2006 |
| EU ELV | Not Relevant |
| Low-Halogen Status | Low-Halogen per IEC 61249-2-21 |
| REACH SVHC | Not Contained per D(2025)7771-DC (04 Feb 2026) |
| EU RoHS | Compliant per EU 2015/863 |

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474

Downloaded from Arrow.com.

- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

---

## Part Details

### General

| | |
|---|---|
| Status | Active |
| Category | Ring and Spade Terminals |
| Series | 19193 |
| Description | VersaKrimp Ring Tongue Terminal for 2/0 AWG Wire, Closed-Brazed Barrel, Stud Size 3/8" (M9), Carton |
| Keyword | Ring Terminal, Ring Terminals |
| Product Name | VersaKrimp |
| Style | Ring |
| Type | Ring Terminal, Metric Ring Terminal |
| UPC | 800755052282 |

### Agency

| | |
|---|---|
| CSA | LR18689 |
| UL | E32244 |

### Physical

| | |
|---|---|
| Barrel Type | Closed - Brazed |
| Insulation | None |
| Material - Plating Mating | Tin |
| Net Weight | 27.216/g |
| Packaging Type | Carton |
| Stud Size | 3/8" (M9) |
| Termination Interface Style | Crimp or Compression |
| Wire Insulation Diameter | 17.25mm max. |
| Wire Size (AWG) | 2/0 |
| Wire Size $mm^2$ | 70.00 |

Downloaded from Arrow.com.

# Application Tooling

This document was generated on Apr 29, 2026

Downloaded from Arrow.com.