

Part Number : [39000380](#)

Product Description : KK 254 Crimp Terminal, 22-28 AWG, 0.35µm Gold (Au), Nickel (Ni) Under-Plate, Phosphor Bronze, Chain

Series Number : 2759

Status : Active

Product Category : Crimp Terminals

Engineering Number : 2759PBG

Documents & Resources

Drawings

[Drawing 039000380_sd.pdf](#)

Specifications

[Product Specification PS-10-07-001.pdf](#)

[Product Specification PS-2759-005-001.pdf](#)

[Product Specification PS-2759-006-001.pdf](#)

[Product Specification PS-5045-003-001.pdf](#)


[Product Specification PS-5045-004-001.pdf](#)

[Product Specification 50510001-000.pdf](#)

[Product Specification 50510002-PS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Compliant per 2000/53/EC
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D

- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	Crimp Terminals
Series	2759
Description	KK 254 Crimp Terminal, 22-28 AWG, 0.35µm Gold (Au), Nickel (Ni) Under-Plate, Phosphor Bronze, Chain
Application	Signal
Product Family	KK Interconnect Systems
Product Name	KK 254
UPC	800753336544

Physical

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	64.000/mg
Packaging Type	Reel
Plating min - Mating	0.356µm
Plating min - Termination	0.356µm, 2.032µm
Termination Interface Style	Crimp or Compression
Wire Insulation Diameter	1.2-1.7mm max.
Wire Size (AWG)	22, 24, 26, 28
Wire Size mm ²	N/A

Use with Part(s)

Description	Part Number
-------------	-------------

KK 254 Single Row Crimp Housings	<u>2695</u>
KK 2.50mm Pitch Single Row Receptacle Housings	<u>5051</u>

Application Tooling

Global

Description	Part Number
Extraction Tool for KK 2.54mm Terminals, 22-30 AWG	<u>11030022</u>
Insertion Tool for KK 2.54mm Terminals, 22-30 AWG	<u>638120000</u>
Mini-Mac Applicator for KK and Cat Ear Terminals for 22-30 AWG Wire with Insulation Diameter 1.09-1.57mm and 22-28 AWG Wire with Insulation Diameter 1.20-1.70mm	<u>638882000</u>
Mini-Mac Applicator for KK and Cat Ear Terminals for 22-30 AWG Wire with Insulation Diameter 0.96-1.20mm	<u>638882100</u>

This document was generated on Jul 29, 2024