
Part Number : 191270013
Product Description : Avikrimp Flanged Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier
Series Number : 19127
Status : Active
Product Category : Ring and Spade Terminals
Engineering Part Number : AA-815-10T



Documents and Resources

Drawings

191270013_sd.pdf

3D Models and Design Files

STEP AP242

SOLIDWORKS

Creo

Specifications

PS-19902-015-001.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)7771-DC (04 Feb 2026)
EU RoHS	Compliant per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Downloaded from Arrow.com.

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Ring and Spade Terminals
Series	19127
Description	Avikrimp Flanged Spade Tongue Terminal for 22-18 AWG Wire, Stud Size 10 (M5), Mylar Tape Carrier
Keyword	Spade Terminal, Spade Terminals
Product Name	Avikrimp
Style	Spade
Type	Spade Connector, Metric Spade Connector
UPC	800753098961

Agency

CSA	LR18689
UL	E32244

Physical

Barrel Type	Closed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Plating Mating	Tin
Net Weight	0.760/g

Downloaded from Arrow.com.

Packaging Type	Adhesive Tape on Reel
Stud Size	10 (M5)
Wire Insulation Diameter	3.56mm max.
Wire Size (AWG)	18, 20, 22
Wire Size mm^2	0.25-1.50

Application Tooling

Global

Description	Part Number
Mini-Mac Applicator	192310584
ATP Crimp Dies for the Tape Crimp Module and ATP-101 & 301 Press	192880023
Mini-Mac Pneumatic Applicator for Ring and Spade Terminals, 22-18 AWG	638851300

Downloaded from Arrow.com.