
Data Sheet | Item Number: 756-1103/060-100


PROFIBUS cable; M12B plug; straight; 5-pole; Length: 10 m


https://www.wago.com/756-1103/060-100





Color: violet





Dimensions in mm

Short description:

- PUR, halogen-free
- Suitable for drag chains
- Silicon- and PVC-free
- High resistance to microbes, hydrolysis, oil, chemicals and UV radiation
- High chemical resistance

Technical data	
Operating voltage	≤ 300 V
Insulation resistance	> 2500 MΩ/km
Conductor resistance	55 Ω/km (max.); Loop resistance: 110 Ω/km (max.)

Downloaded from Arrow.com.

Mechanical data

Weight	744 g
Color	violet

Commercial data

PU (SPU)	1 pcs
Packaging type	Box
Country of origin	DE
GTIN	4045454521615
Customs tariff number	85444290900
End of Sale	2024-05-01
End of Production	2024-05-15
End of Delivery	2024-06-01
End of Service and Repair	2025-06-01

Product Classification

UNSPSC	26121634
eCl@ss 10.0	27-06-18-01
eCl@ss 9.0	27-06-18-01
ETIM 9.0	EC002599
ECCN	NO US CLASSIFICATION

Downloads

Environmental Product Compliance

Compliance Search

Environmental Product Compliance 756-1103/060-100

Documentation

System Description

I/O-SYSTEM – SPEED-WAY, General Product Information	pdf 1035.20 KB	

CAD/CAE-Data

CAE data

WSCAD Universe 756-1103/060-100

Downloaded from Arrow.com.