



Part Number : [1301080097](#)
Product Description : Super-Safeway Twin Tube
64W Fluorescent Work Light 12V, Cord Type 12/3
SJ00W Feed Thru 7.62m (25.0') Cord Length
Series Number : 130108
Status : Active
Product Category : Lamps and Lights
Engineering Number : 1051-12



Documents & Resources

Product Environment Compliance

Compliance

China RoHS	Not Reviewed
EU ELV	Not Reviewed
Low-Halogen Status	Not Reviewed
REACH SVHC	Not Reviewed
EU RoHS	Not Reviewed

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Lamps and Lights
Series	130108
Description	Super-Safeway Twin Tube 64W Fluorescent Work Light 12V, Cord Type 12/3 SJOOW Feed Thru 7.62m (25.0') Cord Length
NEMA Configuration	Non-NEMA
Product Name	Super-Safeway
Type	Wide Area Lamps
UPC	78678867066

Agency

CSA	LR85374
UL	E174254

Electrical

Lamp Wattage - Maximum	64W
Lumens	5300
On/Off Switch	No
Voltage (Fixture) - Maximum	12V AC/DC

Physical

Bulb Type	Fluorescent
Cord Length - Primary	7.62m (25.0')
Cord Length - Secondary	0.152m (6.00")
Cord Type - Primary	12/3 SOOW
Depth	190.75mm (7.510")
Duty	Industrial
Guard Included	No
Guard Type	N/A
Height	82.55mm (3.250")
Lamp Type	F32/T8

Length	1.39m (54.620")
Material - Globe	Butyrate
Material - Guard	Nitrile Rubber 80 Shore A
Mounting Style	Adjustable Brackets
Outlet	Feed-Through
Packaging Type	Carton

This document was generated on Sep 18, 2025