

## VGA High-Resolution RGB Coaxial Cable (HD15 M/F), 6 ft. (1.83 m)

MODEL NUMBER: **P500-006**



Extend the high-resolution connection between your VGA-enabled computer and monitor up to 6 ft. with no ghosting. Recommended for easy access to VGA ports that are hidden or hard to reach.

### Features

#### Extends Connection Between VGA-Enabled Computer and Monitor Up to 6 ft.

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coax (RGB) and paired video wire
- Foil and braid shielding protects against EMI/RFI line noise that can distort or destroy data
- Molded gold-plated HD15 connectors and contacts provide maximum conductivity and minimize data loss
- Integral strain relief protects cable and connectors from stress and cracking
- Rugged PVC jacket designed for long life

## Specifications

| OVERVIEW           |                |
|--------------------|----------------|
| UPC Code           | 037332012296   |
| Product Type       | Passive        |
| Technology         | Coax; VGA/SVGA |
| PHYSICAL           |                |
| Color              | Black          |
| Cable Jacket Color | Black          |
| Cable Length (ft.) | 6              |
| Cable Length (m)   | 1.83           |

### Highlights

- Supports video resolutions up to 2048 x 1536, including 1080p
- Made from mini-coax (RGB) and paired video wire
- Foil and braid shielding blocks hazardous EMI/RFI line noise
- Gold-plated connectors and contacts for maximum conductivity
- Integral strain relief protects against cable stress and cracking

### System Requirements

- Display device with HD15 input

### Package Includes

- P500-006 VGA Coax High-Resolution Monitor Extension Cable (M/F), 6 ft.



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

|                                      |                           |
|--------------------------------------|---------------------------|
| Shipping Dimensions (hwd / cm)       | 17.78 x 22.86 x 1.27      |
| Shipping Dimensions (hwd / in.)      | 7.00 x 9.00 x 0.50        |
| Shipping Weight (kg)                 | 0.26                      |
| Shipping Weight (lbs.)               | 0.58                      |
| <b>CONNECTIONS</b>                   |                           |
| Side A - Connector 1                 | HD15 (MALE)               |
| Side B - Connector 1                 | HD15 (FEMALE)             |
| Latching or Gripping Connector       | No                        |
| <b>FEATURES &amp; SPECIFICATIONS</b> |                           |
| IP68 Rated                           | No                        |
| IP20 Rated                           | No                        |
| <b>STANDARDS &amp; COMPLIANCE</b>    |                           |
| Product Compliance                   | RoHS                      |
| <b>WARRANTY</b>                      |                           |
| Product Warranty Period (Worldwide)  | Lifetime limited warranty |

© 2022 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>