



Overview

Lead time	Usually in Stock
-----------	------------------

Physical

Colour	Black
Depth	6.9 cm
Height	4.4 cm
Net weight	0.06 kg
Width	1.9 cm

Output

Number of power socket outlets	1
--------------------------------	---

Conformance

Product certifications	UL recognized
------------------------	---------------

Environmental

Ambient air temperature for operation	-15...45 °C
Operating altitude	0...10000 ft
Relative humidity	0...95 %
Ambient air temperature for storage	-15...45 °C
Storage altitude	0.00...3048.00 m
Storage Relative Humidity	0...95 %

Surge Protection and Filtering

Data line protection	Cable modem/video protection Coaxial video/cable protection
Data line protected	1
Response time	1 ns common mode
Peak current	0.5 kA common mode

Packing Units

Package 1 Weight	0.28 kg
Package 1 Height	9.9 cm
Package 1 width	3.3 cm
Package 1 Length	9.5 cm
SCC14	30731304217191
Number of Units in Package 2	96
Package 2 Height	206.38 mm
Package 2 width	412.75 mm
Package 2 Length	638.18 mm

Contractual warranty

Warranty	Lifetime
----------	----------