Datasheet for part number DBMM21W1PA101

Our Catalog Part Number: DBMM21W1PA101
Our Global Manufacturing Part Number: 051522-0157
Brand: Cannon Product Category: D Sub Product Line: D Sub Series: COMBO D

Product Datasheet	
General	Combo D Series: D-Subminiature offering mixed layouts
Wire Gauge Range AWG	AWG 8-26
Mating Cycles	500
Contact Arrangement	21W1 (20 contacts size 20, 1 empty size 8 cavities)
Dielectric Withstanding Voltage	1000 VAC at sea level
Current Rating Signal Contacts	7.5 max
Contact Resistance	10 milli Ohm max
Operating Temperature	-55°/+150°
Salt Spray Test	48 hours {96 Hrs for Stainless Steel}
Shell Material	Carbon Steel
Shell Finish	Cadmium plating
Insulator Material	Thermoplastic, type PCT UL 94V-0
Insulator Color	black
Gender	Pin
Contact Type	Solder pot
Contact Material	copper alloy
Contact Finish	gold over nickel (Performance Class 1)
Mounting Method	.120" (3,05mm) Through Hole

Specifications and dimensions subject to change.

Downloaded from Arrow.com.