800310-000 | JM-TRI-40B142SG



Jackmoon Triplex Duct Plug, Size 4.00, for up to 3 cables with outer diameter between 33.0 and 36.1 mm

- Split design for retrofitting without disassembly
- Anchors and organizes subducts or multiple duct systems
- Eliminates duct-edge abrasion to cables
- Excellent for supporting cables at the tops of risers
- Expandable gasket allows for expansion and contraction of cables or subducts without leakage

Product Classification

Brand	Jackmoon®
Product Type	Duct plug, triplex
Regional Availability	EMEA | Latin America | North America

Dimensions

Cable Diameter, maximum	36.10 mm
Cable Diameter, minimum	33.00 mm
Conduit Inner Diameter, maximum	104.90 mm
Conduit Inner Diameter, minimum	100.10 mm
Net Weight	1.7 lb

Environmental Specifications

Environmental Space	Handholes | Manholes
Qualification Standards	IEC 60068-2-17, 5 m waterhead

General Specifications

Application	Cables | Pipes | Subducts
Body Style	Round
Cables/Pipes Supported, quantity	3
Color	Green
Package Quantity	1

Material Specifications

Material Type	PVC
Sealant Type	Chloroprene rubber

Regulatory Compliance/Certifications

Agency	**Classification**

©2019 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: December 12, 2018

COMMSCOPE®

Downloaded from Arrow.com.

RoHS 2011/65/EU	Compliant



©2019 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: December 12, 2018

COMMSCOPE®

Downloaded from Arrow.com.