

Specification Sheet

Part Number: 151-01122



Separates bundles to help prevent chafing and wear.

Single bundles can be mounted on top of the mount, or two bundles can be separated using the two side saddles; giving the mount versatility.

Low profile design allows mount to be placed in areas where space is limited.

Article Number 151-01122

Type LPM25

Color Black (BK)

Quantity Per pack

Product Description Low Profile Mounts secure bundles close to mounting surfaces, making them ideal for applications where bundle mounting space is limited. These are secured with a .25" mechanical fastener, and have a counter bore for easy access with a socket which can be torqued up to 100 in/lbs. The mount accommodates cable ties up to .5" in width.

Short Description Low Profile Screw Mount, 1.8 x 0.98", 0.25" Hole, PA66HIRHSUV, Black, 500/pkg

Global Part Name LPM25-PA66HIRHSUV-BK

Length L (Imperial)	1.8
Length L (Metric)	45.1
Fixation Method	Screw Mounting and Rivet
Width W (Imperial)	0.98
Width W (Metric)	24.9
Cable Ties	T50 - T250
Height H (Imperial)	0.66
Height H (Metric)	16.7
Cable Tie Width Max (Imperial)	0.53
Cable Tie Width Max (Metric)	13.5
Mounting Hole Diameter D (Imperial)	0.25 "
Mounting Hole Diameter D (Metric)	6.7 mm
Mounting Hole Diameter D Max (Metric)	6.7
Material	Polyamide 6.6 high impact modified, heat and UV stabilized (PA66HIRHSUV)

Material Shortcut	PA66HIRHSUV
Flammability	UL 94 HB
UV Resistant (Yes/No)	Yes
Operating Temperature	-40°F to +221°F (-40°C to +105°C)
Reach Compliant (Article 33)	Yes
ROHS Compliant	Yes
Package Quantity (Imperial)	500
Package Quantity (Metric)	500
Customs Number	3926909988

7930 N. Faulkner Road, Milwaukee, WI 53224
 Phone: (800) 537-1512 | Email: corp@htamericas.com

© 2025 HellermannTyton. All Rights Reserved.
[Contact Us](#) [RoHS/WEEE Compliance](#) [Disclaimer](#) [Terms and Conditions](#)