



YAZV2C2TC38FX90

YAZV2C2TC38FX90

Cu compression long barrel flex conductor, 2 holes/W/ insp window, #2 weld(125/24-150/24), #2AWG,3/8" stud, Tin plated,Brown, 10 index

[Image](#) | [Line Art](#) | [3D Model](#) | [Video](#) | [Customer Drawing](#)

 [Email Datasheet](#)

 [Print Datasheet](#)

Photo Not Available



Specifications

Dimensional	General	Conductor(s)	Physical	Approvals / Certifications	Other Features
Dimensional					
Tongue Angle				90 Degree	
Strip Length				1-7/16	
Length (in)				2.17	
Barrell Style				Skived	
Bolt Hole Size (in)				0.39	
Barrel Type				Long	
Thickness				0.10	
B Length (in)				1.38	
Pad Width (in)				0.68	
E - in				1.00	
General					
Number of Holes				2	
Product Description				Cu compression long barrel flex conductor, 2 holes/W/ insp window, #2 weld(125/24-150/24), #2AWG,3/8" stud, Tin plated,Brown, 10 index	
Conductor(s)					
Copper Solid Size (Range)				N/A	
Navy Cable Size (Range)				N/A	
Copper Stranded (Range)				2 AWG	
Physical					
Type of Plating				Tin	
Bolt Hole Size				3/8	
Color Code				Brown	
Plated (Yes or No)				Y	
Index Number				10	
Product Material				Copper	
Approvals / Certifications					
UL Listed				Y	
CSA Certified				Y	
ROHS Compatible				Compliant	
UL Recognized				N	
CULUS				N	
Other Features					
loaded from Arrow.com .				7818101764500	

