


⑩	TIE	2	WHITE L=180mm
⑨	PE BAG	1/5	CLEAR SIZE: 360*380*0.05mm PRINT BLACK"MADE IN CHINA"+"5PCS" .
⑧	PE BAG	1	CLEAR SIZE: 150*280*0.05mm PRINT BLACK"MADE IN CHINA"+"1PC".
⑦	TUBE	2	HEAT SHRINK TUBE BLACK OD1.5*20MM
⑥	SCREW	2	#4-40UNC TYPE L=30mm,NICKEL PLATED,MOLD:BEIGE(IV-29) ABS
⑤	IN JACKET	9g	CLEAR LD-PE (Mould NO.:NM-62)
	OUT JACKET	30g	BEIGE(IV-29) 40P PVC(Mould NO.WM-145)
④	IN JACKET	9g	CLEAR LD-PE (Mould NO.:NM-33)
	OUT JACKET	30g	BEIGE(IV-29) 40P PVC(Mould NO.WM-071)
③	CONN	1	CN 36P MALE SODER TYPE PIN G/F SHELL NI-PLATED INSULATOR COLOR:BLUE
②	CONN	1	DB 25P MALE SODER TYPE PIN G/F SHELL NI-PLATED INSULATOR COLOR:BLUE
①	CABLE	1	NOUL 28AWG*25C+D+AL/MY OD6.5mm JACKET:BEIGE(IV-29) L=7000±20MM
NO.	NAME	Q'TY	SPECIFICATION

Scale	Free					Date	Name	Customer-No.		G	
TOLERANCE						Drawn	20.02.2017	Amy			
						Approved	04.09.2017	Fred	ASSMANN WSW-No.		
									AK159-7		
DIM	TOL	①	Delete the wire color for pin assignment	04.09.2017	Fred				Drawing-No.		H
		②	Drawn	20.02.2017	Amy				ASS 7857 CA	rev01	
Angle	TOL	Id.	Modification	Date	Name				Replace	Sheet	