

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2008

© COPYRIGHT 2008


BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC


DIST

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	D	ADDED PART NUMBER	26JUL2010	H.U	T.M



22POS(X-KEY)
: 2-2013325-1
2-2069573-1
2-2069574-1



RECOMMEND PC BOARD HOLE PATTERN
: CONNECTOR MOUNT SIDE
(NOT ACCUMULATE TOLERANCE)
PC BOARD THICKNESS : 1.0~1.6±0.1

22	35.0	42.3	44.3	X	22	YELLOW	2-2069574-1
						NATURAL	2-2069573-1
						BLACK	2-2013325-1
12	17.5	24.8	26.8	X	12	YELLOW	1-2069574-6
						NATURAL	1-2069573-6
						BLACK	1-2013325-6
3	10.5	17.8	20.2	X	8	YELLOW	1-2069574-4
						BLACK	1-2013325-4
n	A	B	C	KEY	POS.	COLOR	PART NO

①.MATERIAL:HOUSING:66 NYLON GLASS FILLED(UL94V-0)
CONTACT:COPPER ALLOY
RETENTION LEG:PRE-TIN COPPER ALLOY

②.FINISH(ALL OVER):NICKEL PLATING 1.27μmMIN

③.FINISH(CONTACT AREA):GOLD PLATING 0.38μmMIN AFTER ②

④.FINISH(CONTACT TAIL):TIN PLATING 2μmMIN AFTER ②
5.THE SHAPE, SIZE AND POSITION OF THE CHARACTER
SHOW THE OUTLINE.
THEY DON'T SHOW DETAILS.

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS: 単位: 概 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±0.5° 0-PLC ± 1-PLC ± 2-PLC ± 3-PLC ± 4-PLC ± ANGLES ±	DWN M. MAEBASHI 09MAY2008 CHK T. KUDO 09MAY2008 APVD S. MANABE 09MAY2008 PRODUCT SPEC 製品規格 108-78336 APPLICATION SPEC 取付適用規格 - WEIGHT -	Tyco Electronics Corporation Kawasaki, Japan
MATERIAL 材料 ①	FINISH 仕上 ②③④	NAME 名称 DYNAMIC D1900D 3.5mmPITCH HDR ASSY (V-TYPE)	RESTRICTED TO -
		SIZE A3 CAGE CODE 00779 DRAWING NO C-2013325	SCALE 4:1 SHEET 1 OF 2 REV D

CUSTOMER DRAWING

SCALE 4:1

SHEET 1 OF 2 REV D

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

2008

© COPYRIGHT 2008

BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR


DESCRIPTION

DATE


DWN

APVD





SEE SHEET 1 OF 2



12POS(X-KEY) : I-2013325-6
I-2069573-6
I-2069574-6



8POS(X-KEY) : I-2013325-4
I-2069574-4



THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION
SHOULD BE CONTACTED FOR THE LATEST REVISION.

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0. PLC ±
1. PLC ±
2. PLC ±
3. PLC ±
4. PLC ±
ANGLES ±

MATERIAL

FINISH

DWN 09MAY2008

CHK M. MAEBASHI

T. KUDO 09MAY2008

APVD S. MANABE 09MAY2008

PRODUCT SPEC

108-78336

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

Tyco Electronics

Tyco Electronics AMP K.K.
Kawasaki, Japan

NAME

DYNAMIC DI900D 3.5mmPITCH
HDR ASSY (V-TYPE)

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A3

00779

C-2013325

SCALE 4:1

SHEET 2 OF 2

REV D