

Product Line

- DeepTronica >
- Single Pair Ethernet >
- ZConnect >
- Ceres >
- X-Lok >
- M Series >
- FLOS & FLOS+ >
- Power >
- RBL >
 - Middle Size
 - Large Size
 - Accessory
- HS-Lok >
- NMEA 2000 >
- Heavy Duty Shielded >
- RJ >
- USB >
- SSL >
- HDMI >
- DVI >
- Fiber Optic >
- RF >
- Cable Joiner >
- Cable Gland >
- Pressure Relief Vent >
- LED Light Guide >
- D-Sub >



CBD-06RFMC-RC8C20

Operating Temperature: -40°C ~ +105°C
Transmission Speed: N/A
Shielded: Plastic, Non-shielded
Jacket Material: PVC
Certificate: N/A

You must login first for view the price


Quantity - 1 +

 Add to Cart  Inquiry 

Can't find? [Customize your part](#)

Mating Pair & Accessories


Connector Type ▼ Search



RBL, Accessory...
CAP-WACFRPD1
-40°C ~ +105°C

- 0 +


☐



RBL, Middle Size...
CBD-06AMFM-...
-40°C ~ +105°C

- 0 +


☐



RBL, Middle Size...
CBD-06AMFM-...
-40°C ~ +105°C

- 0 +


☐



RBL, Middle Size...
CBD-06AMFM-...
-40°C ~ +105°C

- 0 +


☐



RBL, Middle Size...
CBD-06AMFM-...
-40°C ~ +105°C

- 0 +

☐



RBL, Middle Size...
CBD-06AMFM-...
-40°C ~ +105°C

- 0 +

☐

Add to Cart Inquiry

Specifications	Download / CAD
Nominal Current 10A+5A	Connector Type Receptacle With Wires
Shielded Plastic, Non-shielded	No. of Contacts 06
Connector Gender Female	Backshell Circular
Mating Style Push Lock With Latch	IP Rating IP68
Assembly Style Crimp	
More Options	

People Also Bought

