
Part Number : 734120508
Product Description : MCRF Right-Angle Plug to MCRF Right-Angle Plug on 1.32mm Cable, 55.00mm Length, 50 Ohms
Series Number : 73419
Status : Obsolete
Product Category : RF Cable Assemblies



Obsolete

Documents and Resources

Drawings

734120508_sd.pdf

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2025)4165-DC (25 June 2025)
EU RoHS	Compliant per EU 2015/863

Compliance Statements
- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents
- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest
- PFAS

Downloaded from Arrow.com.

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Obsolete
Category	RF Cable Assemblies
Series	73419
Description	MCRF Right-Angle Plug to MCRF Right-Angle Plug on 1.32mm Cable, 55.00mm Length, 50 Ohms
Application	RF
Assembly Configuration	Dual Ended Connectors
Connector to Connector	MCRF-to-MCRF
Product Name	MCRF
Type	RF Cable Assembly
UPC	822350569415

Electrical

Frequency	6 GHz
Impedance	50Ω

Physical

Cable Length	50.00mm
Gender	Plug/Plug
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Resin	Liquid Crystal Polymer (LCP)
Net Weight	0.280/g
Packaging Type	Bag
Single Ended	No
Wire/Cable Type	1.32mm Coaxial

Solder Process Data

Lead-Free Process Capability	N/A

Obsolete

Downloaded from Arrow.com.

Mates With / Use With

Mates with Part(s)

Description	Part Number
MCRF Cable Assemblies	73412

This document was generated on May 26, 2026

Obsolete

Downloaded from Arrow.com.