

Save 20% On Your Next Order!

Thank you for your business.

[Reveal Your Code >](#)[Browse All Products](#) | [USB](#) | [USB 2.0 Cables](#) | [USB 2.0 A to B Cables](#)

Press image to zoom

2M USB 2.0 A/B CABLE - BLACK (6.6FT)

Connect your USB device to the USB port on your USB hub, PC or Mac®

Product # : 28102

Connector 1 : (1) USB-A Male

Connector 2 : (1) USB-B Male

Colors :

☒ Black ☐ Red ☐ Blue[+ show all colors](#)

Lengths :

☒ 6.6ft ☐ 3.3ft ☐ 9.8ft ☐ 16.4ft

58,306 In Stock & ready to ship!

1

Add



print share chat

Product Info

Customer Reviews

Questions & Answers

Distributors

More Choices

Product Description

Product Features

Product Certifications

Product Specifications

Product Support

Product Description

Just plug-and-play for keyboards, mice, modems, printers, and other USB peripherals. This cable provides a transfer rate up to 480 Mbps depending upon the peripheral's USB version, and easily attaches to any USB device. Foil and braid shielding reduces EMI/RFI interference and twisted pair construction helps reduce crosstalk thus ensuring high speed, error-free data transfer.

WARNING: Cancer and Reproductive Harm www.P65Warnings.ca.gov

Product Features

- Use to connect a printer or camera to a PC
- Prefect replacement cable or extra cable for longer length
- Available in lengths up to 5m

Product Certifications

Tap an icon to learn more:



Product Specifications

Color :	Black
Length :	2.00 Meter
UPC :	757120281023
Warranty :	Lifetime
Vendor :	C2G
Weight :	0.190 LB

- Download a PDF with the technical specifications of this product on the Support tab
- PC and Mac® compatible
- Supports high speed USB 2.0 devices (480 Mbps), and is backwards compliant with full-speed USB 1.1 (12 Mbps) and low speed USB 1.0 (1.5 Mbps).

Electrical Characteristics

- Nominal Impedance with Tolerance - $90\Omega\pm15\%$
- Nominal Capacitance - 131PF/M
- Nominal Velocity of Propagation - 12Mb/s
- DC Resistance - 28AWG 2390hm/Km @20°C, 24AWG 94.20hm/Km @20°C
- Insulation Resistance - $10M\Omega$

Physical characteristics

Conductor 1 (x2)

- Material - Stranded Tinned Copper
- Size - 28AWG (7/0.127 TC)
- Insulation - HD-PE
- OD - 0.85mm
- Color - White/Green (twisted pair)

Conductor 2 (x2)

- Material - Stranded Tinned Copper
- Size - 24AWG (7/0.20 TC)
- Insulation - SR-PVC
- OD - 1.1mm
- Color - Red, Black

Drain Wire

- Material - Tinned Copper
- Size - 28AWG (7/0.12 TC)

Shield 1

- Material - Aluminum Mylar Wrap

Shield 2

- Material - Braided Copper
- Coverage - 65%

Jacket

- Material - PVC
- OD - 4.7mm

USB 2.0 A Connector

- Gender - Male

- Insulation - White PBT
- Contact Material - Gold Flash
- Shell Material - Nickel Plated

USB 2.0 B Connector

- Gender - Male
- Insulation - White PBT
- Contact Material - Gold Flash
- Shell Material - Nickel Plated

Hood Type

- Molded
- Approvals - RoHS Compliant
- Pacakge Type - Polybag

Product Support

Downloads

- Download a version of the [technical specifications](#)

Info

- About Us
- Order History
- Where To Buy
- More ▾

Service

- Contact Us
- OEM Solutions
- Tech Support
- More ▾

Resources

- Connector Guides
- ConnectXpress
- Drivers & Manuals
- More ▾

Have A Question?

- Get help with [Chat](#)
- Call C2G **800.506.9607**



United States | Europe +

Copyright © 2018 C2G. All Rights Reserved

