

**Part Number :** [1300990075](#)

**Product Description :** MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, 90° Angle Male, Cable Diameter 6.35-9.53mm (.250-.375"), Non-Metallic Mesh

**Series Number :** 130099

**Status :** Not Recommended For New Design

**Product Category :** Cable Grips

**Engineering Part Number :** 5525NM



---

## Documents and Resources

### Drawings

[1300990075\\_sd.pdf](#)

---

## Product Environment Compliance

### Compliance

|                    |              |
|--------------------|--------------|
| China RoHS         | Not Reviewed |
| EU ELV             | Not Reviewed |
| Low-Halogen Status | Not Reviewed |
| REACH SVHC         | Not Reviewed |
| EU RoHS            | Not Reviewed |

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

### Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

### Substances of Interest

- PFAS

### EU RoHS Certificate of Compliance

### Additional Product Compliance Information

---

## Part Details

### General

|              |                                                                                                                               |
|--------------|-------------------------------------------------------------------------------------------------------------------------------|
| Status       | Not Recommended For New Design                                                                                                |
| Category     | Cable Grips                                                                                                                   |
| Series       | 130099                                                                                                                        |
| Description  | MAX-LOC Strain Relief Cord-Sealing Grip, 1/2" NPT, 90° Angle Male, Cable Diameter 6.35-9.53mm (.250-.375"), Non-Metallic Mesh |
| NEMA Rating  | NEMA 3R                                                                                                                       |
| Product Name | MAX-LOC                                                                                                                       |
| Type         | Strain Relief Grip                                                                                                            |
| UPC          | 78678855255                                                                                                                   |

### Agency

|     |         |
|-----|---------|
| CSA | LR32159 |
| UL  | E76954  |

### Physical

|                            |                          |
|----------------------------|--------------------------|
| Approximate Break Strength | N/A                      |
| Bale Length                | N/A                      |
| Body Style                 | 90° Angle                |
| Cable Diameter             | 6.35-9.53mm (.250-.375") |
| Color - Grommet            | N/A                      |
| Eye Type                   | N/A                      |
| Gender                     | Male                     |
| Material - Body            | Nylon                    |
| Material - Grip            | Nylon                    |
| Mesh Length                | N/A                      |
| Number of Holes            | 1                        |
| O-Ring                     | No                       |
| Thread Size                | 1/2" NPT                 |

### Mates With / Use With

**Use with Part(s)**

| Description                                     | Part Number       |
|-------------------------------------------------|-------------------|
| MAX-LOC Lock Nut 1/2" NPT                       | <u>1300990143</u> |
| MAX-LOC Gasket Sealing Ring,<br>1/2" NPT, Black | <u>1300990149</u> |
| MAX-LOC O-Ring, 1/2" NPT                        | <u>1301800314</u> |

---

This document was generated on Aug 29, 2026